Product data sheet

Specifications





floor mounting pillar polyester H=800mm for PLM54 and 64

NSYSFSPLMG

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 720.97 USD

Main

Range	Thalassa
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	Support pillar
Device Application	Multi-purpose
Enclosure Nominal Dimensions	-
Mounting Location	On the floor
Range Compatibility	Thalassa Thalassa PLM
Device Composition	fixing elements 1 support pillar 1 floor frame

Complementary

Material	Support pillar polyester charged with fibreglass Floor frame steel
Color	Support pillar Gray RAL 7035)
Fixing Mode	By fixing element
Height	31.50 in (800 mm)
Width	At the base 15.94 in (405 mm) On the top 13.98 in (355 mm)
Depth	At the base 7.87 in (200 mm) On the top 6.50 in (165 mm)

Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480777301
Returnability	No
Country Of Origin	ES

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.66 in (22.0 cm)
Package 1 Width	16.54 in (42.0 cm)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Package 1 Length	32.28 in (82.0 cm)
Package 1 Weight	14.55 lb(US) (6.6 kg)
Unit Type Of Package 2	P12
Number Of Units In Package 2	24
Package 2 Height	66.93 in (170.0 cm)
Package 2 Width	31.50 in (80.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	383.60 lb(US) (174.0 kg)

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations