

Product data sheet

Specifications



Stainless canopy 304L, Scotch Brite® finish. for WM enclosure W600xD250mm

NSYTX6025

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 497.33 USD

Main

Range	Spacial
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Canopy
Application	Multi-purpose
Range Compatibility	Spacial Spacial S3X
For Enclosure Nominal Dimensions	-
Mounting Location	On top of enclosure
Device Composition	1 canopy fixing elements

Complementary

Quantity Per Set	Set of 1
Material	stainless steel 304L
Surface Finish	Scotch-Brite® brushed
Fixing Mode	By fixing element
Height	2.76 in (70 mm)
Width	23.82 in (605 mm)
Depth	11.14 in (283 mm)
Thickness	0.04 in (1 mm)
Net Weight	5.13 lb(US) (2.328 kg)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480156250
Returnability	No
Country Of Origin	BG

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	2.95 in (7.5 cm)
Package 1 Width	12.20 in (31 cm)
Package 1 Length	24.41 in (62 cm)
Package 1 Weight	5.13 lb(US) (2.328 kg)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	50
Package 2 Height	37.40 in (95 cm)
Package 2 Width	39.37 in (100 cm)
Package 2 Length	47.24 in (120 cm)
Package 2 Weight	284.40 lb(US) (129 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free

 RoHS Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations