Product data sheet





Spiral band for cable bundle shaping. Allows cable passage body/ door. Pckg: 50m

NSYTC12100

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 573.29 USD

Main

Accessory / Separate Part Category	Cable management accessory
Product Or Component Type	Cable duct
Range Compatibility	Thalassa Thalassa PLS
	Thalassa Thalassa PLA
	Thalassa Thalassa PLM
	Spacial Spacial SBM
	Spacial Spacial S3D
	Spacial Spacial S3CM
	Spacial Spacial CRN
	Spacial Spacial SM
	Spacial Spacial SF
Anwendung	Multi-purpose
Device Composition	1 50 m reel

Complementary

Material	PE (polyethylene)
Color	colourless
Length	1968.50 in (50000 mm)
Diameter	0.35 in (9 mm) 0.47 in (12 mm)

Environment

Ambient Air Temperature For -76...185 °F (-60...85 °C)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480184512
Returnability	Yes
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15.75 in (40.0 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Width	11.81 in (30.0 cm)
Package 1 Length	7.87 in (20.0 cm)
Package 1 Weight	5.67 lb(US) (2.57 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	20
Package 2 Height	39.37 in (100.0 cm)
Package 2 Width	47.24 in (120.0 cm)
Package 2 Length	7.87 in (20.0 cm)
Package 2 Weight	141.98 lb(US) (64.4 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations