Product data sheet

Specifications





900mm polyester plinth - partly burried - for vers.PLAZ or PLAZT W1000xD320mm

NSYZHPLA103G

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 558.76 USD

Main

Range	Thalassa
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Plinth
Application	Multi-purpose
Nominal Dimensions Of The Housing	-
Device Composition	fixing elements 1 plinth
Range Compatibility	Thalassa Thalassa PLA

Complementary

Fixing Mode	Screwed - bottom of enclosure By fixing element - on floor
Color	Plinth Gray RAL 7035)
Height	35.43 in (900 mm)
Depth	40.75 in (1035 mm)

Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480777837
Returnability	No
Country Of Origin	ES

Packing Units

J	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.72 in (12.0 cm)
Package 1 Width	37.40 in (95.0 cm)
Package 1 Length	42.52 in (108.0 cm)
Package 1 Weight	47.00 lb(US) (21.32 kg)
Unit Type Of Package 2	PAM

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Number Of Units In Package 2	6
Package 2 Height	32.28 in (82.0 cm)
Package 2 Width	39.37 in (100.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	310.68 lb(US) (140.92 kg)

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations