Specifications



Spacial WM enclosure canopy W1200xD400 Colour RAL7035.. Fixings supplied.

NSYTJ12040

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 196.20 USD

Main

Range	Spacial
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Сапору
Application	Multi-purpose
Range Compatibility	Spacial Spacial CRN Spacial Spacial S3D
For Enclosure Nominal Dimensions	-
Mounting Location	On top of enclosure
Device Composition	canopy fixing elements instruction sheet

Complementary

•	5
Material	galvanised steel
Color	Gray RAL 7035)
Surface Finish	Epoxy-polyester powder
Fixing Mode	By 4 screws M6
Height	1.65 in (42 mm)
Width	Nominal 47.24 in (1200 mm) Real 47.60 in (1209 mm)
Depth	Nominal 15.75 in (400 mm) Real 16.32 in (414.5 mm)
Net Weight	16.53 lb(US) (7.5 kg)
Mounting Diameter	0.31 in (8 mm)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480198861
Returnability	No
Country Of Origin	ES

Packing Units

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.17 in (5.5 cm)
Package 1 Width	16.73 in (42.5 cm)
Package 1 Length	48.03 in (122.0 cm)
Package 1 Weight	16.53 lb(US) (7.5 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations