



Stainless canopy 304L, Scotch Brite® finish. for WM enclosure W800xD300mm

NSYTX8030

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 528.51 USD

Main

Range	Spacial
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Canopy
Application	Multi-purpose
Range Compatibility	Spacial Spacial S3X
For Enclosure Nominal Dimensions	-
Mounting Location	On top of enclosure
Device Composition	1 canopy fixing elements

Complementary

Quantity Per Set	Set of 1
Material	stainless steel 304L
Surface Finish	Scotch-Brite® brushed
Fixing Mode	By fixing element
Height	2.76 in (70 mm)
Width	31.69 in (805 mm)
Depth	13.11 in (333 mm)
Thickness	0.04 in (1 mm)
Net Weight	8.19 lb(US) (3.714 kg)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480156267
Returnability	No
Country Of Origin	BG

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Height	3.74 in (9.5 cm)
Package 1 Width	14.57 in (37 cm)
Package 1 Length	32.28 in (82 cm)
Package 1 Weight	8.19 lb(US) (3.714 kg)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	30
Package 2 Height	47.05 in (119.5 cm)
Package 2 Width	39.37 in (100 cm)
Package 2 Length	47.24 in (120 cm)
Package 2 Weight	273.37 lb(US) (124 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations