Product data sheet

Specifications



Busway I-Line Circuit Breaker Plug-in Unit, 20A, FA Frame, 480V, 4 Wire

PFA34020GN

Uiscontinued on: Nov 20, 2023

(!) Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 1,978.00 USD

Main

Product Or Component Type	Plug-in unit
Range Of Product	I-Line
Circuit Breaker Type	FA
Trip Unit Technology	Thermal-magnetic

Complementary

Protection Type	Circuit breaker	
Mounting Mode	Plug-in	
[Ue] Rated Operational Voltage	277/480 V AC	
Line Rated Current	20 A	
Number Of Phases	3 phase	
Poles Description	3P	
Interrupt Rating	25 kA 240 V AC	
	18 kA 480 V AC	
Wiring Configuration	4-wire (integral ground bus)	
Awg Gauge	AWG 14AWG 4 1 phase and neutral	
	AWG 10AWG 2 1 ground	
Depth	8.62 in (219 mm)	
Height	8.27 in (210 mm)	
Width	14.37 in (365 mm)	

Environment

Product Certifications	CSA C22.2 No 27 UL listed file E22182	
Standards	UL 857	

Ordering and shipping details

Category	20182 - PFA / PHD C/B PLUGS	
Discount Schedule	PE7	
Gtin	785901022190	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Returnability	No	
Country Of Origin	US	

Packing Units

	· · · · · · · · · · · · · · · · · · ·
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.00 in (25.4 cm)
Package 1 Width	11.00 in (27.94 cm)
Package 1 Length	15.50 in (39.37 cm)
Package 1 Weight	18.50 lb(US) (8.392 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information
Yes

Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Compliant with Exemptions	
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.	
Environmental Disclosure	Product Environmental Profile	
Circularity Profile	No need of specific recycling operations	
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	