





Automatic switch, PowerPacT P, 1200A, 2 pole, 600VAC, 50kA, lugs, magnetic

PKL26000S12

Main

Product Or Component Type	Automatic switch
Range Of Product	PowerPact P
Trip Unit Technology	Magnetic
Circuit Breaker Type	P-frame

Complementary

•		
Line Rated Current	1200 A	
[Ue] Rated Operational Voltage	600 V AC	
Mounting Mode	Unit mount	
Poles Description	2P	
Short-Circuit Withstand	65 kA 240 V UL 489 50 kA 600 V UL 489 50 kA 480 V UL 489	
Breaking Capacity Code	К	
Electrical Connection	Lugs, line Lugs, load	
Awg Gauge	4 x AWG 3/0500 kcmil (aluminium/copper)	
Terminal Identifier	AL1200P25K	
Magnetic Tripping Current	24000 A	
Height	16.24 in (412.50 mm)	
Width	16.54 in (420.12 mm)	
Depth	14.49 in (368.05 mm)	
Tightening Torque	442.54 lbf.in (50 N.m) 0.150.37 in² (95240 mm²) (AWG 3/0500 kcmil)	

Environment

Product Certifications	CSA	
	UL Listed	
	IEC	

Ordering and shipping details

Category	01215-PG,H,J,K,L,N UNIT MT BREAKERS
Discount Schedule	DE2
Returnability	No
Country Of Origin	US

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	16.22 in (41.2 cm)
Package 1 Width	16.54 in (42.0 cm)
Package 1 Length	14.49 in (36.8 cm)
Package 1 Weight	32.00 lb(US) (14.515 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov