





# Mini circuit breaker, QO, 30A, 2 pole, 120/240VAC, 65kA, plug in

QH230

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 293.00 USD

#### Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	30 A
Voltage Rating	120/240 V AC 120 V AC
Mounting Type	Plug-in
Number Of Poles	2P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Pressure plate

#### Complementary

Interrupt Rating	65 kA 120/240 V AC 65 kA 120 V AC
Number Of Panel Spaces	2
Wire Size	AWG 14AWG 8 copper or aluminium
Tightening Torque	40.71 lbf.in (4.6 N.m)
Height	2.99 in (76 mm)
Width	1.50 in (38 mm)
Depth	2.91 in (74 mm)
Net Weight	0.61 lb(US) (0.277 kg)

#### **Environment**

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

#### Ordering and shipping details

Category	US1DE2A00926
Discount Schedule	DE2A
Gtin	785901012931
Returnability	Yes
Country Of Origin	US

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.60 in (4.064 cm)
Package 1 Width	3.40 in (8.636 cm)
Package 1 Length	3.60 in (9.144 cm)
Package 1 Weight	9.76 oz (276.691 g)

### **Contractual warranty**

Warranty 18 months

Apr 19, 2024



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

#### Well-being performance

<b>⊘</b>	Toxic Heavy Metal Free	
<b>Ø</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes
<b>⊘</b>	Halogen Free Product	

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Circularity Profile	No need of specific recycling operations