





# Busway I-Line Circuit Breaker Plug-in Unit, 300A, M-Frame, 25kA-600V, 3W, Horiz

PTMJ36300GH

! Discontinued on: Nov 20, 2023



Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Product Or Component Type	Plug-in unit
Range Of Product	I-Line
Circuit Breaker Type	M-frame
Trip Unit Technology	Electronic, basic, ET 1.0, LI

### Complementary

Protection Type	Circuit breaker
Mounting Mode	Bolt-on
[Ue] Rated Operational Voltage	600 V AC
Line Rated Current	300 A
Number Of Phases	3 phase
Poles Description	3P
Interrupt Rating	100 kA 240 V AC 65 kA 480 V AC 25 kA 600 V AC
[Ics] Rated Service Short-Circuit Breaking Capacity	80 %
Wiring Configuration	3-wire (integral ground bus)
Awg Gauge	AWG 3/0500 kcmil 3 phase and neutral AWG 6300 kcmil 4 ground
Depth	24.84 in (631 mm)
Height	24.21 in (615 mm)
Width	50.20 in (1275 mm)
Condition Of Use	Horizontal installation

#### **Environment**

Product Certifications	CSA C22.2 No 27 UL listed file E22182	
Standards	UL 857	

## Ordering and shipping details

Category	US10PE720192
Discount Schedule	0PE7

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Returnability No

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	24.21 in (61.5 cm)
Package 1 Width	50.20 in (127.5 cm)
Package 1 Length	24.84 in (63.1 cm)
Package 1 Weight	284.00 lb(US) (128.82 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov