Product data sheet

Specifications





Mini circuit breaker, QO, 15A, 1 pole, 120VAC, 10kA, plug in, 30mA grd fault B, aux switch 1A

QO115EPD1200

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 542.00 USD

Main

Product	Miniature circuit-breaker	
Range	QO	
Current Rating	15 A	
Voltage Rating	120 V AC	
Mounting Type	Plug-in	
Number Of Poles	1P	
Circuit Breaker Type	Ground fault protecting class B 30 mA	
Ratings	HACR rated	
Electrical Connection	Pressure plate	
Options	Auxiliary switch 120 V AC 1A	

Complementary

Interrupt Rating	10 kA 120 V AC
Number Of Panel Spaces	2
Wire Size	AWG 14AWG 8 copper AWG 12AWG 8 aluminium
Tightening Torque	35.40 lbf.in (4 N.m) 40.71 lbf.in (4.6 N.m) 0.010.03 in² (420 mm²) (AWG 12AWG 4)
Height	4.13 in (105 mm)
Width	1.50 in (38 mm)
Depth	2.91 in (74 mm)
Net Weight	0.70 lb(US) (0.318 kg)

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	US1DE2A00910	
Discount Schedule	DE2A	
Gtin	785901218968	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Returnability	No
Country Of Origin	MX

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.50 in (3.8 cm)
Package 1 Width	2.91 in (7.4 cm)
Package 1 Length	4.33 in (11 cm)
Package 1 Weight	11.20 oz (317.515 g)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov