Product data sheet

Specifications



All in one, QO, CSED, ringless socket, 200A, surface mount, 30 spaces, 40 circuits, 22kA SCCR, horn bypass

QC3040M200SH

() Discontinued on: Jun 30, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product Or Component Type	All-In-One
Range Of Product	QO
Meter Socket Type	Ringless
Ниb Туре	A

Complementary

200 A
22 kA
Surface
30
40
10
Lugs, line side Lugs, service ground
AWG 6350 kcmil (aluminium/copper) line side AWG 8AWG 2/0 (aluminium/copper) service ground
Main lugs 250 lb.in, AWG 6350 kcmil, aluminium/copper Service ground 50 lb.in, AWG 3AWG 2/0, aluminium/copper Service ground 45 lb.in, AWG 6AWG 4, aluminium/copper Service ground 40 lb.in, AWG 8, aluminium/copper Branch lugs 50 lb.in, AWG 3AWG 2/0, aluminium/copper Branch lugs 45 lb.in, AWG 6AWG 4, aluminium/copper Branch lugs 45 lb.in, AWG 6AWG 4, aluminium/copper Branch lugs 20 lb.in, AWG 8, aluminium/copper Branch lugs 20 lb.in, AWG 14AWG 10, aluminium/copper Branch lugs 20 lb.in, AWG 12AWG 10, aluminium/copper Cover 10 lb.in
Service disconnect (factory installed)
200 A
200 A
UG OH outdoor
Horn bypass
18.76 in (476.50 mm)
5.41 in (137.41 mm)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Height

Ordering and shipping details

Category	US1DE3A00122
Discount Schedule	DE3A
Gtin	785901876229
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	41.18 in (104.6 cm)
Package 1 Width	18.78 in (47.7 cm)
Package 1 Length	5.39 in (13.7 cm)
Package 1 Weight	65.00 lb(US) (29.484 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information
Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov