

Product data sheet

Specifications



Mini circuit breaker, QO, 20A, 1 pole, 120/240VAC, 65kA, plug in, alarm switch

QH1202100

Discontinued on: Aug 25, 2023

Discontinued

Main

| | |
|-----------------------|-------------------------------|
| Product | Miniature circuit-breaker |
| Range | QO |
| Current Rating | 20 A |
| Voltage Rating | 120/240 V AC 120 V AC |
| Mounting Type | Plug-in |
| Number Of Poles | 1P |
| Circuit Breaker Type | Standard |
| Ratings | HACR and Switching Duty rated |
| Electrical Connection | Pressure plate |
| Options | Alarm switch 120 V AC 1A |

Complementary

| | |
|------------------------|--------------------------------------|
| Interrupt Rating | 65 kA 120/240 V AC 65 kA 120 V AC |
| Number Of Panel Spaces | 2 |
| Wire Size | AWG 14...AWG 8 copper or aluminium |
| Tightening Torque | 40.71 lbf.in (4.6 N.m) |
| Height | 2.99 in (76 mm) |
| Width | 1.50 in (38 mm) |
| Depth | 2.91 in (74 mm) |
| Net Weight | 0.30 lb(US) (0.136 kg) |

Environment

| | |
|----------------|------------------|
| Certifications | UL Listed CSA |
| Ambient Rating | 104 °F (40 °C) |

Ordering and shipping details

| | |
|-------------------|---------------------------|
| Category | 00926-QO IND SPECIALTY CB |
| Discount Schedule | DE2A |
| Returnability | No |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|-------------------|----|
| Country Of Origin | MX |
|-------------------|----|

Packing Units

| | |
|------------------------------|---------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 3.20 in (8.128 cm) |
| Package 1 Width | 3.50 in (8.89 cm) |
| Package 1 Length | 4.70 in (11.938 cm) |
| Package 1 Weight | 4.80 oz (136.078 g) |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Under investigation
