





# Mini circuit breaker, QO, 20A, 1 pole, 120/240VAC, 10kA, plug in, consumer pack

Q0120CP

Product availability: Stock - Normally stocked in distribution

Price\*: 29.10 USD

#### Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	20 A
Voltage Rating	120/240 V AC 120 V AC
Mounting Type	Plug-in
Number Of Poles	1P
Circuit Breaker Type	Standard
Ratings	HACR and Switching Duty rated
Electrical Connection	Pressure plate
Type Of Packing	Consumer packaging

# Complementary

Interrupt Rating	10 kA 120/240 V AC 10 kA 120 V AC
Number Of Panel Spaces	1
Wire Size	AWG 14AWG 8 copper or aluminium
Tightening Torque	35.40 lbf.in (4 N.m)
Height	2.99 in (76 mm)
Width	0.75 in (19 mm)
Depth	2.91 in (74 mm)
Net Weight	0.28 lb(US) (0.127 kg)

#### **Environment**

Certifications	UL Listed CSA	
Ambient Rating	104 °F (40 °C)	

# Ordering and shipping details

Category	US10CPQ01318
Discount Schedule	0CPQ
Gtin	047569837999

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Returnability	Yes	
Country Of Origin	US	

# **Packing Units**

9	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.70 in (1.778 cm)
Package 1 Width	3.00 in (7.62 cm)
Package 1 Length	3.20 in (8.128 cm)
Package 1 Weight	4.48 oz (127.006 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	3.30 in (8.382 cm)
Package 2 Width	3.00 in (7.62 cm)
Package 2 Length	7.70 in (19.558 cm)
Package 2 Weight	2.85 lb(US) (1.293 kg)
Unit Type Of Package 3	CAR
Number Of Units In Package 3	100
Package 3 Height	8.00 in (20.32 cm)
Package 3 Width	6.80 in (17.272 cm)
Package 3 Length	17.50 in (44.45 cm)
Package 3 Weight	28.90 lb(US) (13.109 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

## Well-being performance

<b>⊘</b>	Toxic Heavy Metal Free	
<b>Ø</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes
<b>⊘</b>	Halogen Free Product	

## **Certifications & Standards**

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Compliant with Exemptions	
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.	
Circularity Profile	No need of specific recycling operations	