





Load center, QO, 1 phase, 40 spaces, 40 circuits, 200A convertible main breaker, PoN, NEMA1, 2 x gnd bar, UL

QO140M200PT2

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 1,100.00 USD

Main

Marketing Trade Name	QO
Product Type	Load Center

Complementary

•	
Tightening Torque	Cover 20 lb.in
Pon Convertible Mains (Lugs)	PoN Convertible Mains (breaker)
Rated Current	200 A
Number Of Spaces	40
Max Short Circuit Current Rating	22 kA
Maximum Number Of Single Pole Circuits	40
Maximum Number Of Tandem Breakers	20
Number Of Phases	1 phase
Height	33.78 in (858 mm)
Width	14.25 in (362 mm)
Depth	3.74 in (95 mm)

Environment

Enclosure Rating	NEMA 1 indoor
Ambient Air Temperature For Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	UL Listed

Ordering and shipping details

Category	US1DE3A10001	
Discount Schedule	DE3A	
Gtin	785901616764	
Returnability	No	
Country Of Origin	US	

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.39 in (1.001 cm)
Package 1 Width	0.39 in (1.001 cm)
Package 1 Length	0.39 in (1.001 cm)
Package 1 Weight	21.64 lb(US) (9.816 kg)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov