Product data sheet

Specifications



Load center, QO, 1 phase, 30 spaces, 30 circuits, 200A convertible main lugs, PoN, NEMA1, Qwik-grip, gnd bar, UL

QO130L200PQG

Product availability: Stock - Normally stocked in distribution facility

Price*: 644.76 USD

Main

Marketing Trade Name	QO
Product Type	Load Center
Provided Equipment	Qwik grip assembly kit 1)

Complementary

Complementary	
Tightening Torque	Main lugs 250 lb.in, AWG 4250 kcmil, aluminium/copper
Pon Convertible Mains (Lugs)	PoN Convertible Mains (lugs)
Rated Current	200 A
Number Of Spaces	30
Max Short Circuit Current Rating	65 kA
Maximum Number Of Single Pole Circuits	40
Maximum Number Of Tandem Breakers	10
Number Of Phases	1 phase
Voltage Rating	120/240 V AC
Wire Size	AWG 6300 kcmil aluminium/copper
Ground Bar	Grounding bar included (not installed)
Busbar Material	Copper: busbar
Enclosure Material	Welded sheet steel
Surface Finish	Baked enamel Gray
Box Number	9Q
Height	29.84 in (758 mm)
Width	14.25 in (362 mm)

Environment

Enclosure Rating	NEMA 1 indoor
Ambient Air Temperature For Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	UL Listed

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Category	US1DE3A10003	
Discount Schedule	nt Schedule DE3A	
Gtin	785901774341	
Returnability	Yes	
Country Of Origin	US	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.00 in (10.16 cm)
Package 1 Width	14.44 in (36.672 cm)
Package 1 Length	30.88 in (78.423 cm)
Package 1 Weight	16.83 lb(US) (7.634 kg)

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov