


# Product data sheet

Specifications

SQUARE D



Load center interior, QO, 1 phase, 40 spaces, 40 circuits, 225A convertible main breaker, NEMA1, UL

QO140M225I

! Discontinued

! Discontinued on: Oct 15, 2021

## Main

Product Type	Load Center Interior
Marketing Trade Name	QO
Load Center Type	Main breaker
Rated Current	225 A
Number Of Spaces	40
Max Short Circuit Current Rating	22 kA
Maximum Number Of Single Pole Circuits	40
Maximum Number Of Tandem Breakers	0
Number Of Phases	1 phase
Voltage Rating	120/240 V AC

## Complementary

Ground Bar	Grounding bar (ordered separately)
Busbar Material	Tin plated copper: busbar
Product Certifications	UL Listed

## Environment

Ambient Air Temperature For Operation	23 °F (-5 °C) 104 °F (40 °C)
---------------------------------------	---------------------------------

## Ordering and shipping details

Category	00199-DE5 MISC. SERVICE PARTS
Discount Schedule	DE5
Returnability	No

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

## Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Sustainability





**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant	<a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a>	Pro-active China RoHS declaration (out of China RoHS legal scope)
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>	