Product data sheet

Specifications







Load center, QO, 1 phase, 32 spaces, 38 circuits, 100A convertible main breaker, PoN, NEMA1, UL

QO132M100P

Product availability: Stock - Normally stocked in distribution facility

Price*: 909.00 USD

Main

Marketing Trade Name	QO
Product Type	Load Center

Complementary

oompicinentary	
Tightening Torque	Cover 20 lb.in
Pon Convertible Mains (Lugs)	PoN Convertible Mains (breaker)
Rated Current	100 A
Number Of Spaces	32
Max Short Circuit Current Rating	22 kA
Maximum Number Of Single Pole Circuits	38
Maximum Number Of Tandem Breakers	6
Number Of Phases	1 phase
Ground Bar	Grounding bar (ordered separately)
Box Number	8
Height	26.02 in (661 mm)
Width	14.25 in (362 mm)
Depth	3.74 in (95 mm)
Net Weight	15.54 lb(US) (7.050 kg)

Environment

Enclosure Rating	NEMA 1 indoor	
Ambient Air Temperature For Operation	23 °F (-5 °C) 104 °F (40 °C)	
Product Certifications	UL Listed	

Ordering and shipping details

Category	US1DE3A10001
Discount Schedule	DE3A
Gtin	785901611271
Returnability	Yes

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Country Of Origin	US
Packing Units	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.74 in (9.5 cm)
Package 1 Width	14.25 in (36.2 cm)
Package 1 Length	26.02 in (66.1 cm)

Package 1 Weight 16.00 lb(US) (7.258 kg)

2

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

REACh Declaration
Compliant
EU RoHS Declaration
China RoHS declaration
Pro-active China RoHS declaration (out of China RoHS legal scope)
Product Environmental Profile
No need of specific recycling operations
WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov