





Enclosed molded case switch, QO, 60A, 2 pole, 240VAC, 22kA, air conditioning, NEMA 3R

QO200TR

Product availability: Stock - Normally stocked in distribution

Price\*: 161.00 USD

### Main

Product Type	Enclosed molded case switch Weatherproof enclosure
Range Of Product	QO

### Complementary

Current Rating	60 A
Interrupt Rating	22 kA 240 V AC
Number Of Phases	1 phase
Enclosure Rating	NEMA 3R outdoor
Breaker Compatibility	Circuit breaker QO 2P
For Use With	air conditioner
Product Certifications	UL Listed
Indoor/Outdoor Use	Enclosed outdoor
Surface Finish	Baked enamel Gray
Voltage Rating	240 V AC
Ambient Air Temperature For Operation	104 °F (40 °C)
Height	6.50 in (165 mm)
Width	4.65 in (118 mm)
Depth	3.90 in (99 mm)
Product Weight	3.00 lb(US) (1.361 kg)

## Ordering and shipping details

Category	US1DE2A00044
Discount Schedule	DE2A
Gtin	785901535966
Returnability	Yes
Country Of Origin	US

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Height	3.50 in (8.89 cm)
Package 1 Width	4.20 in (10.668 cm)
Package 1 Length	6.50 in (16.51 cm)
Package 1 Weight	3.00 lb(US) (1.361 kg)
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	7.10 in (18.034 cm)
Package 2 Width	9.80 in (24.892 cm)
Package 2 Length	19.80 in (50.292 cm)
Package 2 Weight	30.35 lb(US) (13.767 kg)
Unit Type Of Package 3	PAL
Number Of Units In Package 3	400
Package 3 Height	42.00 in (106.68 cm)
Package 3 Width	40.00 in (101.6 cm)
Package 3 Length	48.00 in (121.92 cm)
Package 3 Weight	1270.00 lb(US) (576.062 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov