





Generator panel, QO, 1 phase, 4 spaces, 8 circuits, 30A main breaker with interlock, NEMA3R, gnd bar, UL

QO1DM10030TRBR

Product availability: Stock - Normally stocked in distribution facility

Price\*: 848.00 USD

### Main

Marketing Trade Name	QO	
Product Type	Panel	
Enclosure Type	Weatherproof enclosure	
Cover Type	Surface cover	

### Complementary

Pon Convertible Mains (Lugs)	Main breaker	
Rated Current	100 A	
Number Of Spaces	4	
Max Short Circuit Current Rating	10 kA	
Maximum Number Of Single Pole Circuits	8	
Maximum Number Of Tandem Breakers	4	
Number Of Phases	1 phase	
Wire Size	AWG 8AWG 2 copper	
Ground Bar	Grounding bar (factory installed)	
Electrical Connection	Lugs	
Wiring Configuration	3-wire	
Busbar Material	Tin plated aluminium: busbar	
Enclosure Material	Welded galvannealed steel	
Surface Finish	Baked enamel Gray	
Box Number	17R	
Height	12.64 in (321 mm)	
Width	8.90 in (226 mm)	

### **Environment**

Enclosure Rating	NEMA 3R outdoor
Ambient Air Temperature For Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	UL Listed

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

# Ordering and shipping details

Category	US1DE3A00101 DE3A	
Discount Schedule		
Gtin	785901883227	
Returnability	Yes	
Country Of Origin	MX	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.80 in (12.192 cm)
Package 1 Width	10.20 in (25.908 cm)
Package 1 Length	14.50 in (36.83 cm)
Package 1 Weight	11.39 lb(US) (5.166 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov