





Mini circuit breaker, QO, 30A, 3 pole, 120/240VAC, 10kA, plug in, consumer pack

QO330CP

Product availability: Stock - Normally stocked in distribution

Price*: 248.00 USD

Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	30 A
Voltage Rating	120/240 V AC 240 V AC 120 V AC
Mounting Type	Plug-in
Number Of Poles	3P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Pressure plate
Type Of Packing	Consumer packaging

Complementary

· · · · · · · · · · · · · · · · · ·	
Interrupt Rating	10 kA 120/240 V AC 10 kA 240 V AC
	10 kA 120 V AC
Number Of Panel Spaces	3
Wire Size	AWG 14AWG 8 copper or aluminium
Tightening Torque	35.40 lbf.in (4 N.m)
Height	2.99 in (76 mm)
Width	2.24 in (57 mm)
Depth	2.91 in (74 mm)
Net Weight	0.81 lb(US) (0.367 kg)

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	US10CPQ01330
Discount Schedule	0CPQ

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Gtin	047569071850
Returnability	Yes
Country Of Origin	US

Packing Units

r aciming Critic	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.60 in (6.604 cm)
Package 1 Width	2.20 in (5.588 cm)
Package 1 Length	3.00 in (7.62 cm)
Package 1 Weight	12.95 oz (367.0 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	3
Package 2 Height	3.40 in (8.636 cm)
Package 2 Width	2.20 in (5.588 cm)
Package 2 Length	6.80 in (17.272 cm)
Package 2 Weight	2.52 lb(US) (1.143 kg)
Unit Type Of Package 3	CAR
Number Of Units In Package 3	36
Package 3 Height	3.50 in (8.89 cm)
Package 3 Width	14.20 in (36.068 cm)
Package 3 Length	21.50 in (54.61 cm)
Package 3 Weight	31.24 lb(US) (14.17 kg)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

Ø	Toxic Heavy Metal Free	
Ø	Mercury Free	
②	Rohs Exemption Information	Yes
⊘	Halogen Free Product	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Circularity Profile	No need of specific recycling operations