





Mini circuit breaker, QO, 40A, 2 pole, 120/240VAC, 10kA, plug in, Powerlink

QO240PL

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 543.00 USD

Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	40 A
Voltage Rating	120/240 V AC 240 V AC 120 V AC
Mounting Type	Plug-in
Number Of Poles	2P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs

Complementary

Interrupt Rating	10 kA 120/240 V AC 10 kA 240 V AC 10 kA 120 V AC
Number Of Panel Spaces	2
Provided Equipment	18 in (457.20 mm) lead
Wire Size	AWG 12AWG 2 aluminium AWG 14AWG 2 copper
Tightening Torque	44.25 lbf.in (5 N.m)
Height	4.57 in (116 mm)
Width	1.50 in (38 mm)
Depth	2.91 in (74 mm)
Net Weight	0.86 lb(US) (0.390 kg)

Environment

Certifications	UL Listed CSA	
Ambient Rating	104 °F (40 °C)	

Ordering and shipping details

Category US1DE8A00912

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Discount Schedule	DE8A
Gtin	785901095774
Returnability	Yes
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.10 in (10.414 cm)
Package 1 Width	2.40 in (6.096 cm)
Package 1 Length	5.50 in (13.97 cm)
Package 1 Weight	13.76 oz (390.089 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance



Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov