

# Product data sheet

Specifications

SQUARE D



Mini circuit breaker, QO, 10A, 1 pole, 120/240VAC, 22kA, bolt on, ring

QOB110VH5237

⚠ Discontinued on: Jan 11, 2023

⚠ Discontinued

## Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	10 A
Voltage Rating	120/240 V AC 120 V AC
Mounting Type	Bolt-on
Number Of Poles	1P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Ring tongue

## Complementary

Interrupt Rating	22 kA 120/240 V AC 22 kA 120 V AC
Number Of Panel Spaces	1
Wire Size	AWG 14...AWG 8 copper
Tightening Torque	40.71 lbf.in (4.6 N.m)
Height	2.99 in (76 mm)
Width	0.75 in (19 mm)
Depth	2.91 in (74 mm)
Net Weight	0.32 lb(US) (0.145 kg)

## Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

## Ordering and shipping details

Category	00015-QOB CIRCUIT BREAKERS
Discount Schedule	DE2
Gtin	00785901187738
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin	MX
-------------------	----

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.70 in (1.778 cm)
Package 1 Width	3.20 in (8.128 cm)
Package 1 Length	3.30 in (8.382 cm)
Package 1 Weight	5.12 oz (145.15 g)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability





**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
<hr/>		
Eu Rohs Directive		Compliant
		<a href="#">EU RoHS Declaration</a>
<hr/>		
China Rohs Regulation		<a href="#">China RoHS declaration</a>
		Pro-active China RoHS declaration (out of China RoHS legal scope)
<hr/>		