





Mini circuit breaker, QO, 10A, 1 pole, 120/240VAC, 10kA, bolt on, AC shunt

QOB1101021

Discontinued on: Jan 31, 2024



Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product	Miniature circuit-breaker	
Range	QO	
Current Rating	10 A	
Voltage Rating	120/240 V AC 120 V AC	
Mounting Type	Bolt-on	
Number Of Poles	1P	
Circuit Breaker Type	Standard	
Ratings	HACR rated	
Electrical Connection	Pressure plate	
Options	Shunt trip 120/208/240 V AC	

Complementary

Interrupt Rating	10 kA 120/240 V AC 10 kA 120 V AC	
Number Of Panel Spaces	2	
Wire Size	AWG 14AWG 8 copper or aluminium	
Tightening Torque	35.40 lbf.in (4 N.m)	
Height	2.99 in (76 mm)	
Width	1.50 in (38 mm)	
Depth	2.91 in (74 mm)	
Net Weight	0.67 lb(US) (0.304 kg)	

Environment

Certifications	UL Listed CSA	
Ambient Rating	104 °F (40 °C)	

Ordering and shipping details

Category	US10DE200015	
Discount Schedule	0DE2	
Gtin	3606486144237	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.20 in (8.128 cm)
Package 1 Width	3.60 in (9.144 cm)
Package 1 Length	4.70 in (11.938 cm)
Package 1 Weight	0.67 lb(US) (0.304 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

Ø	Toxic Heavy Metal Free	
Ø	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov