





Mini circuit breaker, QO, 20A, 2 pole, 120/240VAC, 10kA, bolt on, 6mA grd fault A, pigtail

QOB220GFI

Product availability: Stock - Normally stocked in distribution

Price*: 444.00 USD

Main

Product	Miniature circuit-breaker	
Range	QO	
Current Rating	20 A	
Voltage Rating	120/240 V AC 120 V AC	
Mounting Type	Bolt-on	
Number Of Poles	2P	
Circuit Breaker Type	Ground fault protecting class A 6 mA	
Ratings	Not rated	
Electrical Connection	Pressure plate	

Complementary

Interrupt Rating	10 kA 120/240 V AC	
	10 kA 120 V AC	
Number Of Panel Spaces	2	
Wire Size	AWG 14AWG 8 copper	
	AWG 12AWG 8 aluminium	
Tightening Torque	35.40 lbf.in (4 N.m)	
	40.71 lbf.in (4.6 N.m) 0.010.03 in ² (420 mm ²) (AWG 12AWG 4)	
Height	4.13 in (105 mm)	
Width	1.50 in (38 mm)	
Depth	2.91 in (74 mm)	
Net Weight	0.96 lb(US) (0.435 kg)	

Environment

Certifications	UL Listed CSA	
Ambient Rating	104 °F (40 °C)	

Ordering and shipping details

Category	US10DE200015	
Discount Schedule	0DE2	
Gtin	785901563020	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Returnability	Yes
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.20 in (5.588 cm)
Package 1 Width	3.50 in (8.89 cm)
Package 1 Length	5.40 in (13.716 cm)
Package 1 Weight	15.36 oz (435.449 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov