





# Mini circuit breaker, QO, 60A, 2 pole, 120/240VAC, 22kA, bolt on

QOB260VH

Product availability: Stock - Normally stocked in distribution facility

Price\*: 184.68 USD

### Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	60 A
Voltage Rating	120/240 V AC 240 V AC 120 V AC
Mounting Type	Bolt-on
Number Of Poles	2P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs

# Complementary

Interrupt Rating	22 kA 120/240 V AC 22 kA 240 V AC 22 kA 120 V AC	
Number Of Panel Spaces	2	
Wire Size	AWG 8AWG 2 copper or aluminium	
Tightening Torque	49.56 lbf.in (5.6 N.m)	
Height	3.11 in (79 mm)	
Width	1.50 in (38 mm)	
Depth	2.91 in (74 mm)	
Net Weight	0.74 lb(US) (0.336 kg)	

## **Environment**

Certifications	UL Listed CSA	
Ambient Rating	104 °F (40 °C)	

# Ordering and shipping details

Category	US10DE200015	
Discount Schedule	0DE2	
Gtin	785901054788	
Returnability	Yes	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin US

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.50 in (3.81 cm)
Package 1 Width	3.40 in (8.636 cm)
Package 1 Length	3.80 in (9.652 cm)
Package 1 Weight	11.84 oz (335.658 g)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

## Well-being performance

<b>②</b>	Mercury Free	
	Rohs Exemption Information	Yes
<b>⊘</b>	Halogen Free Product	

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Cadmium and cadmium compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov