

Product data sheet

Specifications



Mini circuit breaker, QO, 125A, 3 pole, 120/240VAC, 22kA, bolt on

QOB3125VH

Product availability: Stock - Normally stocked in distribution facility

Price*: 1,953.72 USD

Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	125 A
Voltage Rating	120/240 V AC 240 V AC 120 V AC
Mounting Type	Bolt-on
Number Of Poles	3P
Circuit Breaker Type	Standard
Ratings	Not rated
Electrical Connection	Box lugs

Complementary

Interrupt Rating	22 kA 120/240 V AC 22 kA 240 V AC 22 kA 120 V AC
Number Of Panel Spaces	6
Wire Size	AWG 4...300 kcmil copper or aluminium
Tightening Torque	49.56 lbf.in (5.6 N.m)
Height	5.71 in (145 mm)
Width	4.49 in (114 mm)
Depth	4.88 in (124 mm)
Net Weight	0.96 lb(US) (0.435 kg)

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	US10DE200015
Discount Schedule	0DE2
Gtin	785901065470
Returnability	Yes

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Country Of Origin	MX
-------------------	----

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.30 in (10.922 cm)
Package 1 Width	5.00 in (12.7 cm)
Package 1 Length	6.80 in (17.272 cm)
Package 1 Weight	3.95 lb(US) (1.792 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	558
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	2216.00 lb(US) (1005.16 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



RoHS/REACH

Well-being performance

<div>✓</div> Mercury Free	
<div>✓</div> Rohs Exemption Information	Yes
<div>✓</div> Halogen Free Product	

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Cadmium and cadmium compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov