





Mini circuit breaker, QO, 40A, 3 pole, 120/240VAC, 10kA, bolt on, AC shunt

QOB3401021

Product availability: Stock - Normally stocked in distribution facility

Price*: 482.00 USD

Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	40 A
Voltage Rating	120/240 V AC 240 V AC 120 V AC
Mounting Type	Bolt-on
Number Of Poles	3P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs
Options	Shunt trip 120/208/240 V AC

Complementary

Interrupt Rating	10 kA 120/240 V AC	
	10 kA 240 V AC	
	10 kA 120 V AC	
Number Of Panel Spaces	4	
Wire Size	AWG 8AWG 2 copper or aluminium	
Tightening Torque	44.25 lbf.in (5 N.m)	
Height	3.11 in (79 mm)	
Width	2.99 in (76 mm)	
Depth	2.91 in (74 mm)	
Net Weight	1.17 lb(US) (0.531 kg)	

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	US10DE200015
Discount Schedule	0DE2

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Gtin	785901494423	
Returnability	Yes	
Country Of Origin	MX	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.50 in (8.89 cm)
Package 1 Width	3.20 in (8.128 cm)
Package 1 Length	4.60 in (11.684 cm)
Package 1 Weight	18.72 oz (530.703 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

Ø	Toxic Heavy Metal Free	
Ø	Mercury Free	
②	Rohs Exemption Information	Yes
⊘	Halogen Free Product	

Certifications & Standards

REACh Declaration
Compliant with Exemptions
China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
No need of specific recycling operations