

Product data sheet

Specifications

SQUARE D



Main breaker, QO, 30A, 2 pole,
120/240VAC, 10kA, bolt on

QOM30L

Product availability: Stock - Normally stocked in distribution facility

Price*: 301.50 USD

Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	30 A
Voltage Rating	120/240 V AC
Mounting Type	Bolt-on
Number Of Poles	2P
Circuit Breaker Type	Standard
Ratings	Primary main breaker
Electrical Connection	Lugs
Frame Size	QOM1

Complementary

Interrupt Rating	10 kA 120/240 V AC
Wire Size	AWG 12...AWG 2/0 copper or aluminium
Tightening Torque	53.10 lbf.in (6 N.m) 0.01...0.10 in² (4...65 mm²) (AWG 12...AWG 2/0)
Net Weight	1.27 lb(US) (0.576 kg)
Load Center Type	Main breaker
Number Of Phases	1 phase
For Use With	QO load center
Breaker Compatibility	Load center QO

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	US1DE2A00157
Discount Schedule	DE2A
Gtin	785901114840
Returnability	No
Country Of Origin	MX

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.30 in (10.922 cm)
Package 1 Width	4.20 in (10.668 cm)
Package 1 Length	5.30 in (13.462 cm)
Package 1 Weight	20.32 oz (576.062 g)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant with Exemptions

China Rohs Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information.

California Proposition 65

WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov