

# Product data sheet

Specifications

SQUARE D

Green Premium™



Replacement cover, QO, for 30 space load center with 125A mains, combination flush and surface, gray

QOC30U125C

Product availability: Stock - Normally stocked in distribution facility

Price\*: 39.60 USD

## Main

Marketing Trade Name	QO
Product Type	Load Center Cover

## Complementary

Cover Type	Combination flush/surface cover
Product Compatibility	For indoor load center
Surface Finish	Baked enamel Gray
Number Of Spaces	30
Height	31.06 in (788.92 mm)
Width	15.44 in (392.18 mm)
Depth	0.7 in (17.78 mm)
Rated Current	125 A
Tightening Torque	Cover 2.3 N.m

## Ordering and shipping details

Category	US1DE3A00001
Discount Schedule	DE3A
Gtin	785901967422
Returnability	Yes
Country Of Origin	MX

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.00 in (2.54 cm)
Package 1 Width	15.56 in (39.527 cm)
Package 1 Length	16.25 in (41.275 cm)
Package 1 Weight	10.04 lb(US) (4.554 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>