





# Mini circuit breaker, QOU, 10A, 1 pole, 120/240 VAC, 10kA, ring terminal

QOU1105283

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 67.00 USD

### Main

Product Or Component Type	Miniature circuit-breaker
Range Of Product	QOU
Circuit Breaker Type	Standard
Circuit Breaker Application	HACP rated

## Complementary

Line Rated Current	10 A
Electrical Connection	ring tongue, line side ring tongue, load side
[Ue] Rated Operational Voltage	120/240 V AC 120 V AC 48 V DC
Mounting Mode	Unit mount
Awg Gauge	AWG 14AWG 2 aluminium/copper
Height	4.05 in (102.87 mm)
Width	0.75 in (19.05 mm)
Depth	2.95 in (74.93 mm)
Tightening Torque	45 lbf.in (5.08 N.m) (AWG 14AWG 2)

#### **Environment**

Product Certifications	IEC UL Listed
	CSA

# Ordering and shipping details

Category	US10DE200900
Discount Schedule	0DE2
Gtin	785901475552
Returnability	Yes
Country Of Origin	MX

# **Packing Units**

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Units In Package 1	1
Package 1 Height	3.10 in (7.874 cm)
Package 1 Width	1.00 in (2.54 cm)
Package 1 Length	4.70 in (11.938 cm)
Package 1 Weight	5.75 oz (163.0 q)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

## Well-being performance

<b>⊘</b>	Toxic Heavy Metal Free	
<b>Ø</b>	Mercury Free	
<b>②</b>	Rohs Exemption Information	Yes
<b>⊘</b>	Halogen Free Product	

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Circularity Profile	No need of specific recycling operations