





# Mini circuit breaker, QOU, 100A, 3 pole, 240 VAC, 10kA

QOU3100

Product availability: Stock - Normally stocked in distribution facility

Price\*: 416.00 USD

#### Main

Product Or Component Type	Miniature circuit-breaker	
Range Of Product	QOU	
Circuit Breaker Type	Standard	
Circuit Breaker Application	HACR rated	

#### Complementary

Line Rated Current	100 A	
Electrical Connection	Slotted box lugs, line side Slotted box lugs, load side	
[Ue] Rated Operational Voltage	120/240 V AC 240 V AC	
	120 V AC 60 V DC	
Mounting Mode	Unit mount	
Awg Gauge	AWG 12AWG 2/0 aluminium/copper	
Height	4.45 in (113.03 mm)	
Width	2.25 in (57.15 mm)	
Depth	2.95 in (74.93 mm)	
Tightening Torque	45 lbf.in (5.08 N.m) (AWG 12AWG 2/0)	

#### **Environment**

<b>Product Certifications</b>	UL Listed	
	IEC	
	CSA	

### Ordering and shipping details

Category	US10DE200900	
Discount Schedule	0DE2	
Gtin	785901060338	
Returnability	Yes	
Country Of Origin	MX	

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Height	2.60 in (6.604 cm)	
Package 1 Width	3.50 in (8.89 cm)	
Package 1 Length	4.80 in (12.192 cm)	
Package 1 Weight	23.20 oz (657.709 g)	

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

#### Well-being performance

<b>②</b>	Mercury Free	
<b>②</b>	Rohs Exemption Information	Yes
	Halogen Free Product	

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Cadmium and cadmium compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov