

# Product data sheet

Specifications

SQUARE D



Mini circuit breaker, QOU, 30A, 3 pole, 240 VAC, 10kA, four point quick connect terminals

QOUQ330

⚠ Discontinued on: Jan 11, 2023

⚠ Discontinued

## Main

Product Or Component Type	Miniature circuit-breaker
Range Of Product	QOU
Circuit Breaker Type	Standard
Circuit Breaker Application	HACR rated

## Complementary

Line Rated Current	30 A
Electrical Connection	Slotted box lugs, line side Slotted box lugs, load side
[Ue] Rated Operational Voltage	120/240 V AC 240 V AC 120 V AC 48 V DC
Mounting Mode	Unit mount
Awg Gauge	AWG 14...AWG 2 aluminium/copper
Height	4.05 in (102.87 mm)
Width	2.25 in (57.15 mm)
Depth	2.95 in (74.93 mm)
Tightening Torque	45 lbf.in (5.08 N.m) (AWG 14...AWG 2)

## Environment

Product Certifications	IEC CSA UL Listed
------------------------	-------------------------

## Ordering and shipping details

Category	00900-QOU BREAKERS & SWITCH
Discount Schedule	DE2
Returnability	No
Country Of Origin	MX

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	2.50 in (6.35 cm)
Package 1 Width	3.60 in (9.144 cm)
Package 1 Length	4.80 in (12.192 cm)
Package 1 Weight	17.44 oz (494.416 g)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Halogen Free Product	
Eu Rohs Directive		Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation		<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)