





# Mini circuit breaker, QOU, 50A, 3 pole, 240VAC, 10kA

QOU350

Product availability: Stock - Normally stocked in distribution facility

Price\*: 307.80 USD

#### Main

Product Or Component Type	Miniature circuit-breaker
Range Of Product	QOU
Circuit Breaker Type	Standard
Circuit Breaker Application	HACR rated

#### Complementary

o op. o o o y	
Line Rated Current	50 A
Electrical Connection	Slotted box lugs, line side
	Slotted box lugs, load side
[Ue] Rated Operational Voltage	120/240 V AC
	240 V AC
	120 V AC
	48 V DC
	40 V DO
Mounting Mode	Unit mount
Awg Gauge	AWG 14AWG 2 aluminium/copper
Height	4.05 in (102.87 mm)
Width	2.25 in (57.15 mm)
Depth	2.95 in (74.93 mm)
Tightening Torque	45 lbf.in (5.08 N.m) (AWG 14AWG 2)

## **Environment**

Product Certifications	CSA	
	IEC	
	UL Listed	

### Ordering and shipping details

Category	US10DE200900
Discount Schedule	0DE2
Gtin	785901418986
Returnability	Yes
Country Of Origin	MX

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Height	3.50 in (8.89 cm)
Package 1 Width	4.80 in (12.192 cm)
Package 1 Length	2.60 in (6.604 cm)
Package 1 Weight	18.40 oz (521.631 g)
Unit Type Of Package 2	CAR
Number Of Units In Package 2	5
Package 2 Height	3.50 in (8.89 cm)
Package 2 Width	13.50 in (34.29 cm)
Package 2 Length	20.50 in (52.07 cm)
Package 2 Weight	23.20 lb(US) (10.523 kg)
Unit Type Of Package 3	PAL
Number Of Units In Package 3	840
Package 3 Height	40.00 in (101.6 cm)
Package 3 Width	40.00 in (101.6 cm)
Package 3 Length	48.00 in (121.92 cm)
Package 3 Weight	966.00 lb(US) (438.17 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

# Well-being performance



#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Cadmium and cadmium compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov