





Mini circuit breaker, QOU, 50A, 3 pole, 240 VAC, 10kA, four point quick connect terminals

QOUQ350

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 311.00 USD

Main

Product Or Component Type	Miniature circuit-breaker		
Range Of Product	QOU		
Circuit Breaker Type	Standard		
Circuit Breaker Application	HACR rated		

Complementary

Line Rated Current	50 A	
Electrical Connection	Slotted box lugs, line side	
	Slotted box lugs, load side	
[Ue] Rated Operational Voltage	120/240 V AC	
	240 V AC	
	120 V AC	
	48 V DC	
Mounting Mode	Unit mount	
Awg Gauge	AWG 14AWG 2 aluminium/copper	
Height	4.05 in (102.87 mm)	
Width	2.25 in (57.15 mm)	
Depth	2.95 in (74.93 mm)	
Tightening Torque	45 lbf.in (5.08 N.m) (AWG 14AWG 2)	

Environment

Product Certifications	IEC
	UL Listed CSA

Ordering and shipping details

Category	US10DE200900
Discount Schedule	0DE2
Gtin	785901621058
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCF		

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Units In Package 1	1
Package 1 Height	3.50 in (8.89 cm)
Package 1 Width	4.80 in (12.192 cm)
Package 1 Length	2.60 in (6.604 cm)
Package 1 Weight	18.40 oz (521.631 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance



Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Cadmium and cadmium compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov