Product data sheet

Specifications





APC Replacement Battery Cartridge #11 with 2 Year Warranty

RBC11

Overview

Lead Time Usually in Stock

Main

Product Or Component Type	Replacement battery cartridge
Number Of Cables	1
Battery Type	Lead-Acid battery
Provided Equipment	All required connectors Battery recycling guide Reusable packaging Installation guide

Batteries & Runtime

Battery Slots Empty	0
Included Battery Modules	0
Device Mounting	Stand alone battery stack
Additional Information	RBC 11 is composed of two seperate battery cells. The Net dimensions are measured per cell.
Rbc Quantity	1

Physical

_	
Color	Black
Height	6.81 in (17.3 cm)
Width	5.59 in (14.2 cm)
Depth	7.20 in (18.3 cm)
Net Weight	53.51 lb(US) (24.27 kg)
Mounting Mode	Not rack-mountable
Usb Compatible	No

Environmental

Ambient Air Temperature For Operation	32104 °F (040 °C)
Operating Altitude	010000 ft
Relative Humidity	095 %
Ambient Air Temperature For Storage	5113 °F (-1545 °C)
Storage Altitude	050000 ft (0.0015240.00 m)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Gtin	731304003335
Country Of Origin VN	

Packing Units

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.91 in (27.7 cm)
Package 1 Width	11.61 in (29.5 cm)
Package 1 Length	21.18 in (53.8 cm)
Package 1 Weight	58.82 lb(US) (26.68 kg)

Contractual warranty

Warranty 2 years repair or replace



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >







Take-back Transparency RoHS/REACh

Resource performance



Take-Back Program Available

Well-being performance



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov