





All in one, Homeline, CSED, ringless socket, 100A, surface mount, 16 spaces, 24 circuits, 10kA SCCR, no bypass

RC1624M100S

Product availability: Stock - Normally stocked in distribution facility

Price*: 744.00 USD

Main

Product Or Component Type	All-In-One
Range Of Product	Homeline
Meter Socket Type	Ringless
Hub Type	A

Complementary

Line Rated Current	100 A	
Short-Circuit Current	10 kA	
Mounting	Surface	
Number Of Spaces	16	
Number Of Circuits	24	
Number Of Tandem Breakers	8	
Electrical Connection	Lugs, line side Lugs, service ground	
Wire Size	AWG 6AWG 2/0 (aluminium) line side AWG 6AWG 2/0 (copper) line side AWG 6AWG 2/0 (aluminium) service ground AWG 6AWG 2/0 (copper) service ground	
Disconnect	Service disconnect (factory installed)	
Disconnect Rating	100 A	
Branch Breaker Rating	100 A	
Service Feed Location	OH UG	
Bypass Type	No bypass	
Width	14.77 in (375.16 mm)	
Depth	5.55 in (140.97 mm)	
Height	27.00 in (685.80 mm)	
Bus Rating	125.0 A	

Ordering and shipping details

Category US1DE3A00148

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Discount Schedule	DE3A
Gtin	785901308843
Returnability	Yes
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.10 in (15.494 cm)
Package 1 Width	15.30 in (38.862 cm)
Package 1 Length	26.40 in (67.056 cm)
Package 1 Weight	30.38 lb(US) (13.78 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov