Product data sheet

Specifications



Meter mains, QO, ringless socket, 200A, surface mount, lever bypass

RCM200SL

Product availability: Stock - Normally stocked in distribution facility

Price*: 1,950.00 USD

Main

Product Or Component Type	Meter Mains
Range Of Product	00

Complementary	
Line Rated Current	200 A
Short-Circuit Current	10 kA
Network Number Of Phases	1
Meter Socket Type	Ringless
Mounting	Surface
Number Of Spaces	0
Number Of Circuits	0
Number Of Tandem Breakers	0
Ниb Туре	A
Electrical Connection	Lugs, line side Lugs, service ground
Wire Size	AWG 8AWG 1/0 aluminium/copper)service ground AWG 6350 kcmil aluminium/copper)line side
Disconnect	Service disconnect (ordered separately)
Main Breaker Rating	200 A
Service Feed Location	OH UG
Bypass Type	Class 320 lever bypass
Height	24.00 in (609.60 mm)
Width	24.44 in (620.78 mm)
Depth	4.94 in (125.48 mm)

Environment

Product Certifications

UL E-6294

Ordering and shipping details

Category	US1DE3A00022	
Discount Schedule	DE3A	
Gtin	785901985594	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Returnability	Yes
Country Of Origin	US

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.80 in (14.732 cm)
Package 1 Width	24.50 in (62.23 cm)
Package 1 Length	27.30 in (69.342 cm)
Package 1 Weight	60.00 lb(US) (27.216 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	14
Package 2 Height	36.00 in (91.44 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	885.80 lb(US) (401.79 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information
Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov