





Meter mains, QO, CSED, ringless socket, 200A, surface mount, no bypass, Florida Meter Group

RC2M200SFMG

! Discontinued on: Jun 30, 2023



Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product Or Component Type	Meter Mains
Range Of Product	QO

Complementary

Line Rated Current	200 A
Short-Circuit Current	22 kA
Network Number Of Phases	1
Meter Socket Type	Ringless
Mounting	Surface (outdoor)
Number Of Spaces	0
Number Of Circuits	0
Number Of Tandem Breakers	0
Hub Type	A
Electrical Connection	Lugs, line side Lugs, service ground
Wire Size	AWG 6300 kcmil aluminium/copper)line side AWG 8AWG 2/0 2 aluminium/copper)service ground
Tightening Torque	Lugs 250 lb.in, AWG 6350 kcmil, aluminium/copper Lugs 250 lb.in, AWG 4250 kcmil, aluminium/copper Service ground 50 lb.in, AWG 3AWG 2/0, aluminium/copper Service ground 45 lb.in, AWG 6AWG 4, aluminium/copper Service ground 40 lb.in, AWG 8, copper Lugs 50 lb.in, AWG 3AWG 2/0, aluminium/copper Lugs 45 lb.in, AWG 6AWG 4, aluminium/copper Lugs 40 lb.in, AWG 8, copper Cover 10 lb.in
Disconnect	Service disconnect (ordered separately)
Main Breaker Rating	200 A
Service Feed Location	OH UG
Bypass Type	No bypass
Marking	Florida metering group
Height	23.03 in (584.96 mm)
Width	24.04 in (610.62 mm)
Depth	4.67 in (118.62 mm)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Environment

Product Certifications UL E-6294

Ordering and shipping details

Category	US1DE3A00022
Discount Schedule	DE3A
Gtin	785901063308
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.10 in (18.034 cm)
Package 1 Width	27.00 in (68.58 cm)
Package 1 Length	27.00 in (68.58 cm)
Package 1 Weight	29.50 lb(US) (13.381 kg)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov