Product data sheet

Specifications

SQUARE 🗩



All in one, Homeline, CSED, ringed socket, 200A, surface mount, 20 spaces, 40 circuits, 22kA SCCR, no bypass, solar ready

SC2040M200PS

Product availability: Stock - Normally stocked in distribution facility

Price*: 1,671.00 USD

Main

Product Or Component Type	All-In-One
Range Of Product	Homeline
Meter Socket Type	Ringed
Hub Type	A

Complementary

Complementary	
Line Rated Current	200 A
Short-Circuit Current	22 kA
Mounting	Surface
Number Of Spaces	20
Number Of Circuits	40
Number Of Tandem Breakers	20
Electrical Connection	Lugs, line side Lugs, service ground
Wire Size	AWG 4250 kcmil (aluminium/copper) line side AWG 14AWG 2/0 (aluminium/copper) service ground
Tightening Torque	Main lugs 250 lb.in, AWG 4250 kcmil, aluminium/copper Service ground 50 lb.in, AWG 14AWG 2/0, copper Service ground 50 lb.in, AWG 12AWG 2/0, aluminium Branch lugs 50 lb.in, AWG 14AWG 2/0, copper Branch lugs 50 lb.in, AWG 12AWG 2/0, aluminium Branch lugs 35 lb.in, AWG 12AWG 2/0, aluminium/copper Branch lugs 25 lb.in, AWG 6AWG 4, aluminium/copper Branch lugs 20 lb.in, AWG 14AWG 10, aluminium/copper Branch lugs 20 lb.in, AWG 12AWG 10, aluminium/copper Cover 10 lb.in
Disconnect Rating	200 A
Branch Breaker Rating	200 A
Service Feed Location	OH UG
Bypass Type	No bypass
Connections - Terminals	Plug-on neutral
Color	Grey
Product Compatibility	Solar ready

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Width	21.50 in (546.10 mm)
Depth	5.79 in (147.07 mm)
Height	30.39 in (771.91 mm)
Bus Rating	225.0 A

Environment

Nema Rating

NEMA 3R

Ordering and shipping details

Category	US1DE3A00148
Discount Schedule	DE3A
Gtin	785901342267
Returnability	Yes
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.70 in (19.56 cm)
Package 1 Width	22.30 in (56.64 cm)
Package 1 Length	30.60 in (77.72 cm)
Package 1 Weight	52.70 lb(US) (23.904 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	10
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	42.00 in (106.68 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	563.51 lb(US) (255.602 kg)

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information
Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov