

# Product data sheet

Specifications

SQUARE D



Surge protection device,  
Surgelogic, 480kA, 480 VAC delta,  
3 phase, 3 wire, NEMA 4X

SSP05EMA48S

⚠ Discontinued on: Apr 3, 2023

⚠ Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

## Main

Product	Surge protection device
Range	Surgelogic
Device Short Name	EMA

## Complementary

Voltage Rating	480 V delta AC
Mcov	640 V
Sccr	200 kA
Surge Current	480 kA
Nominal Discharge Current	20 kA
Number Of Phases	3 phase
Wiring Configuration	3-wire
Connection	Lugs AWG 10...AWG 2 copper 35.40 lbf.in (4 N.m)
Local Signalling	Status LED green per phase normal operation Status LED red per phase fault
Provided Equipment	Alarm enable/disable switch Surge counter Dry contacts
Cable Length	19.02 in (483 mm)
Device Mounting	Surface
Height	22.67 in (575.8 mm)
Width	11.70 in (297.2 mm)
Depth	9.40 in (238.8 mm)

## Environment

Ambient Operating	149 °F (65 °C)
Enclosure Rating	NEMA 4X
Enclosure Material	Stainless Steel
Standards	CSA C22.2 No 8 UL 1449:ed. 4 UL 1283:ed. 5

## Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Category	US1DE1B08464
Discount Schedule	DE1B
Gtin	3606486148884
Returnability	No

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	22.68 in (57.6 cm)
Package 1 Width	11.69 in (29.7 cm)
Package 1 Length	9.41 in (23.9 cm)
Package 1 Weight	45.20 lb(US) (20.502 kg)

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Eu Rohs Directive

Compliant with Exemptions

China Rohs Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information.

California Proposition 65

WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)