

# Product data sheet

Specifications

SQUARE D



Surge protection device,  
Surgelogic, 320kA, 600Y/347  
VAC, 3 phase, 4 wire, NEMA 1,  
disconnect switch

SSP08EMA32D

! Discontinued

! Discontinued on: Apr 3, 2023

Product availability: Non-Stock - Not normally stocked in  
distribution facility

## Main

Product	Surge protection device
Range	Surgelogic
Device Short Name	EMA

## Complementary

Voltage Rating	600Y/347 V AC
Mcov	420 V
Sccr	200 kA
Surge Current	320 kA
Nominal Discharge Current	20 kA
Rated Current	150 A
Number Of Phases	3 phase
Max Number Of Poles	3
Wiring Configuration	4-wire
Connection	Lugs AWG 10...AWG 3/0 copper 35.40 lbf.in (4 N.m)
Local Signalling	Status LED green per phase normal operation Status LED red per phase fault
Provided Equipment	Alarm enable/disable switch Surge counter Switch-disconnector with integrated switch for off/on/automatic Dry contacts
Cable Length	19.02 in (483 mm)
Device Mounting	Surface
Height	21.61 in (549 mm)
Width	9.88 in (251 mm)
Depth	7.87 in (200 mm)

## Environment

Ambient Operating	149 °F (65 °C)
Enclosure Rating	NEMA 1
Enclosure Material	Gray painted sheet steel

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Standards	CSA C22.2 No 8 UL 1449:ed. 4 UL 1283:ed. 5
-----------	--

## Ordering and shipping details

Category	US1DE1B08464
Discount Schedule	DE1B
Gtin	3606486148969
Returnability	No

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	21.61 in (54.9 cm)
Package 1 Width	9.88 in (25.1 cm)
Package 1 Length	7.87 in (20.0 cm)
Package 1 Weight	20.50 lb(US) (9.299 kg)

# Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

 Rohs Exemption Information	Yes
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>