Product data sheet

Specification





heat sink, Harmony Solid State Relays, thermal resistance 0.2 degree C W

SSRHP02

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 121.60 USD

Main

Range Of Product	Harmony Solid State Relays
Product Or Component Type	Heat sink

Complementary

Product Compatibility	1 solid state relay SSR panel	
Thermal Resitance	0.2 °C/W	
Mounting Support	Panel	
Material	Aluminium	
Surface Finish	Black anodized	
Surface And Useful Surface	1057.58 in² (6823 cm²)	
Number Of Mounting Holes	6 UNC 8-32	
Tightening Torque	15.0519.47 lbf.in (1.72.2 N.m)	
Sale Per Indivisible Quantity	1	
Width	9.75 in (247.7 mm)	
Height	9.84 in (250 mm)	
Depth	2.28 in (57.9 mm)	
Net Weight	5.71 lb(US) (2.592 kg)	

Ordering and shipping details

Category	US10CP222375
Discount Schedule	0CP2
Gtin	3606480580253
Returnability	No
Country Of Origin	CN

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.25 in (10.8 cm)
Package 1 Width	6.77 in (17.2 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Length	6.77 in (17.2 cm)	
Package 1 Weight	3.33 lb(US) (1.51 kg)	
Unit Type Of Package 2	S03	
Number Of Units In Package 2	4	
Package 2 Height	11.81 in (30.0 cm)	
Package 2 Width	11.81 in (30.0 cm)	
Package 2 Length	15.75 in (40.0 cm)	
Package 2 Weight	13.32 lb(US) (6.04 kg)	



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
Circularity Profile	No need of specific recycling operations
China Rohs Regulation	China RoHS declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Reach Regulation	REACh Declaration

Dimensions Drawings

Dimensions

