

# Product data sheet

Specifications



## Ethernet ConneXium cable - shielded twisted pair - 2 x rugged RJ45 - CE - 5 m

TCSECE3M3M5S4

Product availability: Non-Stock - Not normally stocked in  
distribution facility

### Main

Range Of Product	ConneXium
Accessory / Separate Part Category	Connection accessories
Accessory / Separate Part Type	Connecting cable
Product Or Component Type	Shielded twisted pair straight cable
Accessory / Separate Part Destination	Ethernet network
Cable Length	16.40 ft (5 m)

### Complementary

Transmission Support Medium	Twisted shielded pairs cable
Communication Network Category	5e
Awg Gauge	AWG 24
Electrical Connection	2 connectors, RJ45 straight 8
Marking	CE
Cover Material	PUR

### Environment

Ip Degree Of Protection	IP20
Standards	IEC 11801 class D EN 50173 class D EIA/TIA-568 category CAT 5E
Flame Retardance	Class C2 conforming to CEI 322/1 Class C2 conforming to NF C 32070-1

### Ordering and shipping details

Category	US1PC4118225
Discount Schedule	PC41
Gtin	3595864142975
Returnability	No
Country Of Origin	TH

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	0.87 in (2.200 cm)
Package 1 Width	7.28 in (18.500 cm)
Package 1 Length	7.87 in (20.000 cm)
Package 1 Weight	8.89 oz (252.000 g)
Unit Type Of Package 2	S02
Number Of Units In Package 2	15
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	9.04 lb(US) (4.100 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability




**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	<a href="#">Yes</a>
<b>Eu Rohs Directive</b>	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>	
<b>China Rohs Regulation</b>	<a href="#">China RoHS declaration</a>	
<b>California Proposition 65</b>	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>	