

# Product data sheet

Specifications



rolled ribbon connecting cable - for I/O module with HE10 connectors - 3 m

TSXCDP302

Product availability: Non-Stock - Not normally stocked in distribution facility

## Main

Range Of Product	Modicon Premium Automation platform
Accessory / Separate Part Designation	Rolled ribbon connecting cable
Accessory / Separate Part Type	Connecting cable
Accessory / Separate Part Category	Connection accessories
Accessory / Separate Part Destination	Telefast 2 sub-base I/O module fitted with HE10 connectors
Product Specific Application	Encoder supply 5 V/10...30 V DC Auxiliary inputs supply 24 V DC

## Complementary

Product Compatibility	ABE7H08R10 TSXCTY2C ABE7H16R20
Cable Length	9.84 ft (3 m)
Electrical Connection	2 connectors HE10, 20 ways
Wire Section	0.00 in² (0.08 mm²)
Awg Gauge	AWG 28
Current Per Channel	0.1 A
Net Weight	0.55 lb(US) (0.25 kg)

## Ordering and shipping details

Category	US1PC1422556
Discount Schedule	PC14
Gtin	3389110603095
Returnability	No
Country Of Origin	US

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.59 in (1.5 cm)
Package 1 Width	6.30 in (16.0 cm)
Package 1 Length	7.09 in (18.0 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	6.17 oz (175.0 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	20
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	7.72 lb(US) (3.5 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

## Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
-------------------	---

China Rohs Regulation	<a href="#">China RoHS declaration</a>
-----------------------	--

Environmental Disclosure	<a href="#">Product Environmental Profile</a>
--------------------------	---

Circularity Profile	No need of specific recycling operations
---------------------	--

California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
---------------------------	---