

Product data sheet

Specifications



Fipio trunk cable to be fitted with M23 connectors - 500 m - Ø 8 mm

TSXFPCA500

⚠ Discontinued on: Dec 2, 2020

⚠ To be end-of-service on: Dec 31, 2027

⚠ Discontinued - Service only

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Accessory / Separate Part Designation	Trunk cable to be fitted with M23 connectors
Accessory / Separate Part Type	Connecting cable
Accessory / Separate Part Category	Connection accessories
Accessory / Separate Part Destination	Fipio bus Fipway network

Complementary

Range Compatibility	Advantys STB distributed I/O solutions Modicon Premium automation platform
Cable Length	1640.42 ft (500 m)
Cable Outer Diameter	0.31 in (8 mm)
Type Of Cable	1 shielded twisted pair
Electrical Connection	Free end
Ohmic Cable Resistance	150 Ohm
Net Weight	66.14 lb(US) (30 kg)

Environment

Environmental Characteristic	Normal environment
------------------------------	--------------------

Ordering and shipping details

Category	US1PC1422556
Discount Schedule	PC14
Gtin	3389110830064
Returnability	No
Country Of Origin	IT

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	17.72 in (45.0 cm)
Package 1 Width	23.62 in (60.0 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	23.62 in (60.0 cm)
Package 1 Weight	89.29 lb(US) (40.5 kg)
Unit Type Of Package 2	P06
Number Of Units In Package 2	1
Package 2 Height	18.11 in (46.0 cm)
Package 2 Width	23.62 in (60.0 cm)
Package 2 Length	31.50 in (80.0 cm)
Package 2 Weight	104.72 lb(US) (47.5 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Toxic Heavy Metal Free	
✓ Mercury Free	
✓ Rohs Exemption Information	Yes

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to www.p65warnings.ca.gov