

Product data sheet

Specifications



Fipio trunk cable to be fitted with M23 connectors - 100 m - Ø 7.9 mm - 150 Ohm

TSXFPCR100

⚠ Discontinued - Service only

⚠ Discontinued on: Dec 2, 2020

⚠ To be end-of-service on: Dec 31, 2027

Main

Accessory / Separate Part Designation	Trunk cable to be fitted with M23 connectors
Accessory / Separate Part Type	Connecting cable
Accessory / Separate Part Category	Connection accessories
Accessory / Separate Part Destination	Fipway network Fipio bus

Complementary

Range Compatibility	Modicon Premium automation platform
Cable Length	328.08 ft (100 m)
Cable Outer Diameter	0.31 in (7.9 mm)
Type Of Cable	1 shielded twisted pair
Electrical Connection	Free end
Ohmic Cable Resistance	150 Ohm
Net Weight	16.93 lb(US) (7.68 kg)

Environment

Environmental Characteristic	Harsh environment
------------------------------	-------------------

Ordering and shipping details

Category	22556-TSX MICRO, PL7 MICRO & ACCESS
Discount Schedule	PC14
Gtin	3389110717556
Returnability	No
Country Of Origin	IT

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.72 in (12.0 cm)
Package 1 Width	11.81 in (30.0 cm)
Package 1 Length	11.81 in (30.0 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	14.07 lb(US) (6.384 kg)
------------------	-------------------------

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability




Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration	
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to www.p65warnings.ca.gov	