

# Product data sheet

Specifications



## Vijeo Designer - update 6.2 license - configuration software

VJDUPDTGAV62M

⚠ Discontinued on: Jan 31, 2024

Product availability: Stock - Normally stocked in distribution facility

⚠ Discontinued

### Main

|                              |  |
|------------------------------|--|
| Range Of Product             | Vijeo Designer   |
| Product Or Component Type    | Configuration software   |
| Format                       | DVD-ROM  |
| Type Of License              | Single (1 station)   |
| Software Version             | V6.2   |
| Operating System Requirement | Windows 7 Professional 32/64 bit<br>Windows 8.1<br>Windows 10 Professional 32/64 bit |
| Language                     | German<br>Italian<br>English<br>Spanish<br>Chinese<br>French<br>Portuguese           |

### Complementary

|                             |   |
|-----------------------------|---|
| Provided Equipment          | Vijeo Designer software<br>Acrobat Reader   |
| Audio Video Coding Standard | JPEG  |
| Communication Port Protocol | UniTE TCP/IP<br>Ethernet/IP Explicit<br>Toyopuc PC3J<br>USB<br>Sysmacway<br>Modbus TCP master<br>Simatic<br>Profibus DP<br>ELAU PacDrive<br>Modbus 32-bit extensions<br>Uni-Telway<br>Modbus Plus<br>Fipio/Fipway<br>ROC Plus<br>MELSEC<br>Modbus RTU master<br>Allen-Bradley |
| Previous Software Version   | V6.1  |
| Software Designation        | Vijeo Designer  |
| Software Function           | 34 western alphabets<br>9999 alarms<br>8000 variables<br>4 asian alphabets<br>Sharing up to 300 variables<br>2 middle eastern alphabets   |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                     |  |
|---------------------|--|
| Range Compatibility | Harmony XBT GT<br>Harmony STO & STU<br>Harmony XBT GH<br>Harmony HMI GTO<br>Harmony iPC<br>Harmony XBT GK<br>Harmony XBT GTW<br>Harmony Smart<br>Harmony Compact iPC |
|---------------------|--|

## Ordering and shipping details

|                   |               |
|-------------------|---------------|
| Category          | US10MC222569  |
| Discount Schedule | 0MC2          |
| Gtin              | 3606480712890 |
| Returnability     | Yes           |
| Country Of Origin | FR            |

## Packing Units

|                              |                        |
|------------------------------|------------------------|
| Unit Type Of Package 1       | PCE                    |
| Number Of Units In Package 1 | 1                      |
| Package 1 Height             | 0.79 in (2.000 cm)     |
| Package 1 Width              | 5.28 in (13.400 cm)    |
| Package 1 Length             | 6.22 in (15.800 cm)    |
| Package 1 Weight             | 3.84 oz (109.000 g)    |
| Unit Type Of Package 2       | S02                    |
| Number Of Units In Package 2 | 16                     |
| Package 2 Height             | 5.91 in (15.000 cm)    |
| Package 2 Width              | 11.81 in (30.000 cm)   |
| Package 2 Length             | 15.75 in (40.000 cm)   |
| Package 2 Weight             | 4.60 lb(US) (2.086 kg) |

## Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

 Toxic Heavy Metal Free

 Mercury Free

 Rohs Exemption Information [Yes](#)

|                          |   |
|--------------------------|---|
| <b>Eu Rohs Directive</b> | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a> |
|--------------------------|---|

|                              |   |
|------------------------------|---|
| <b>China Rohs Regulation</b> | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
|------------------------------|---|