# Product data sheet

Specifications





### power cable, between servomotor BDH, BSH and servodrive, 4x1.5mm<sup>2</sup>+2x1mm<sup>2</sup>, 5m

VW3M5101R50

Product availability: Stock - Normally stocked in distribution facility

#### Price\*: 140.19 USD

#### Main

Product Or Component Type	Power cable
Accessory / Separate Part Type	Preassembled power cordset
Accessory / Separate Part Category	Connection accessory
Product Compatibility	Servo motor BMH, 1 2.76 in (70 mm))
	Servo motor BMH, 2 2.76 in (70 mm))
	Servo motor BMH, 3 2.76 in (70 mm))
	Servo motor BMH, 1 3.94 in (100 mm))
	Servo motor BMH, 2 3.94 in (100 mm))
	Servo motor BMH, 3 3.94 in (100 mm))
	Servo motor BMH, 1 5.51 in (140 mm))
	Servo motor BSH, 1 2.17 in (55 mm))
	Servo motor BSH, 2 2.17 in (55 mm))
	Servo motor BSH, 3 2.17 in (55 mm))
	Servo motor BSH, 1 2.76 in (70 mm))
	Servo motor BSH, 2 2.76 in (70 mm))
	Servo motor BSH, 3 2.76 in (70 mm))
	Servo motor BSH, 1 3.94 in (100 mm))
	Servo motor BSH, 2 3.94 in (100 mm))
	Servo motor BSH, 3 3.94 in (100 mm))
	Servo motor BSH, 1 5.51 in (140 mm))
Accessory / Separate Part Destination	Between servo motor and servo drive
Range Compatibility	Lexium 05
	Lexium 32
	Lexium 15
Cable Length	16.40 ft (5 m)
Cable Composition	4 x 1.5 mm <sup>2</sup> + 2 x 1 mm <sup>2</sup>

#### Complementary

Electrical Connection	Connector - industrial M23 servo motor side Free end servo drive side
Net Weight	2.67 lb(US) (1.21 kg)

### Ordering and shipping details

Category	US1PC5118263
Discount Schedule	PC51
Gtin	3389119207300
Returnability	Yes
Country Of Origin	US

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

# **Packing Units**

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.36 in (6.000 cm)
Package 1 Width	10.63 in (27.000 cm)
Package 1 Length	10.63 in (27.000 cm)
Package 1 Weight	2.72 lb(US) (1.236 kg)
Unit Type Of Package 2	P06
Number Of Units In Package 2	60
Package 2 Height	29.53 in (75.000 cm)
Package 2 Width	23.62 in (60.000 cm)
Package 2 Length	31.50 in (80.000 cm)
Package 2 Weight	192.95 lb(US) (87.520 kg)

## **Contractual warranty**

Warranty

18 months

### Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free

#### **Certifications & Standards**

California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
Circularity Profile	End of Life Information
Environmental Disclosure	Product Environmental Profile
China Rohs Regulation	China RoHS declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Reach Regulation	REACh Declaration