# Product data sheet

Specifications





## power cordset 4x1,5mm<sup>2</sup> + 2x1mm<sup>2</sup> + 2x0,14mm<sup>2</sup> 10 m one end w M23 industrial con.

VW3M5501R100

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Price\*: 355.08 USD

#### Main

Range Of Product	Altivar
Accessory / Separate Part Type	Power cable
Accessory / Separate Part Category	Connection accessories
Accessory / Separate Part Destination	Between synchronous motor and variable speed drive
Range Compatibility	Altivar Machine ATV320 Altivar 32
Cable Length	32.81 ft (10 m)
Type Of Cable	Shielded cable
Complementary	

•		
Product Compatibility	Synchronous motor BMP 5.51 in (140 mm), 1 C	
	Synchronous motor BMP 5.51 in (140 mm), 1 F	
	Synchronous motor BMP 5.51 in (140 mm), 2 C	
	Synchronous motor BMP 2.76 in (70 mm), 1 R	
	Synchronous motor BMP 2.76 in (70 mm), 1 F	
	Synchronous motor BMP 2.76 in (70 mm), 2 R	
	Synchronous motor BMP 2.76 in (70 mm), 2 F	
	Synchronous motor BMP 3.94 in (100 mm), 1 R	
	Synchronous motor BMP 3.94 in (100 mm), 1 F	
	Synchronous motor BMP 3.94 in (100 mm), 2 R	
	Synchronous motor BMP 3.94 in (100 mm), 2 F	
Electrical Connection	1 connector M23 8 synchronous motor side	
	1 free end variable speed drive side	
Cable Composition	4 x 1.5 mm² + 2 x 1 mm² + 2 x 0.14 mm²	
Net Weight	5.38 lb(US) (2.44 kg)	

# Ordering and shipping details

Category	US1PC5118263
Discount Schedule	PC51
Gtin	3606480564536
Returnability	No
Country Of Origin	CZ

#### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Package 1 Height	2.17 in (5.500 cm)
Package 1 Width	16.42 in (41.700 cm)
Package 1 Length	14.88 in (37.800 cm)
Package 1 Weight	6.02 lb(US) (2.730 kg)

## **Contractual warranty**

Warranty

18 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

## Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free

#### **Certifications & Standards**

California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
Circularity Profile	End of Life Information
Environmental Disclosure	Product Environmental Profile
China Rohs Regulation	China RoHS declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Reach Regulation	REACh Declaration